

Transport X²



Portable Onsite DGA

Dissolved Gas Analysis (DGA) and moisture measurement of insulating fluids are recognized as the most important tests for condition assessment of fluid-insulated transformers. Every year asset owners deploy field crews to take thousands of fluid samples from transformers as part of periodic health checks and for immediate operational decisions. These samples are sent to offsite laboratories for analysis. Transport X² is a portable 'lab in a box' delivering detailed analysis with dramatically reduced turnaround times. In critical situations, the ability to perform DGA in less than 30 minutes on the spot, empowers asset owners to determine a transformer's condition onsite and thereby allow operational decisions to be made at the earliest opportunity.

GE was the first to deliver consumable-free DGA products to the market and the Transport X² represents the next generation of its portable system. GE's class leading Photo-acoustic spectroscopy (PAS) gas measurement technology, now in its fourth generation, provides laboratory-challenging levels of precision in a calibration free, easy-to-use and hand-carriable product.

Benefiting from over 40 years of global DGA experience, the Kelman™ Transport X² encapsulates intuitive advancements to bring improved performance, innovative new features, enhanced user experience and greater robustness.

Key Benefits

- Measurement of seven diagnostic gases and moisture content in the oil
- Fast diagnostics in less than 30 minutes
- Intuitive touchscreen interface with step-by-step instructions and Plug and Play connectivity
- Compatible with mineral insulating oils and newer ester-based fluids (natural and synthetic)
- Enables operators to effectively respond to alarms, trip events and supports on-site field decision making
- Ideal companion to GE's range of single gas online DGA monitors for adding transformer diagnostics

Applications

As the average age of generation, transmission and distribution transformers increases, the risk of rapid deterioration and even catastrophic failures also increases. Transformer changes can occur in between rounds of periodic laboratory DGA analysis and this risk exposure can go unnoticed. The Transport X² offers electric utility and industrial customers accurate, economical and portable DGA and diagnostics in an easy-to-use handy instrument that is applicable for:

- Mission critical industrial transformers
- Distribution transformers
- Buchholz relay gas
- Tap changer tanks
- Instrument transformers
- Oil filled circuit breakers

Fully Portable

- Standalone DGA field instrument capable of measuring seven diagnostic gases and moisture
- Calibration and consumable gas free design for autonomous field operation
- Robust design with IP67 rating when closed
- Unit weighs less than 9 kg (20 lb)

Field Proven Technology

- Advanced PAS technology (4th generation) underpinned by decades of DGA experience
- Designed and built to GE's high quality standards
- Supports mineral oil and ester fluids
- 5 year warranty as standard

Intuitive Operation

- Graphical touchscreen user interface
- Intuitive onscreen step-by-step instructions
- Seamless integration with Perception software
- Plug and Play download of measurements and log files using standard USB 2.0 memory stick

Built-in Diagnostics

- Built-in internationally recognized DGA diagnostic software tools
- Color graphical display to facilitate visualization
- Storage capacity for >20,000 measurements
- Further diagnostic capabilities through data upload to the Perception software suite



Application Example

The Kelman Transport X² remains your ideal partner for use in conjunction with GE's range of single gas online DGA monitors. These units (such as Hydran™ 201Ti and Hydran M2-X) monitor the transformer and raise an alarm when an abnormal level of fault gas is reached or when the rate of change of this gas level increases rapidly so that you can take action and protect your transformer early in the process.

Such events often require further investigation before a valid conclusion can be reached. Traditional methods require an oil sample to be sent to a laboratory for analysis. This can be a lengthy process before a diagnosis and related decision can be made. However, with the Transport X², the sample can be taken and analyzed onsite, giving comprehensive diagnostic information in less than 30 minutes. The Transport X² data can then be uploaded and visualized in GE's powerful Perception software alongside the readings from the online monitor.



Technical Specification

MEASUREMENT RANGE		TECHNOLOGY		FEATURES	
Hydrogen (H ₂)	5 – 5,000 ppm	Automated headspace gas extraction		LCD Size	6.5 inch color touchscreen
Carbon Monoxide (CO)	2 – 50,000 ppm	Photo-acoustic spectroscopy (PAS) gas measurements (4th gen.)		LCD Type	Resistive touchscreen
Carbon Dioxide (CO ₂)	40 – 50,000 ppm	Thin film capacitive moisture sensor		Screen Resolution	640 x 480
Methane (CH ₄)	2 – 50,000 ppm	Oil and Buchholz gas injection utilizing syringes		Computer interface	USB
Acetylene (C ₂ H ₂)	0.5 – 50,000 ppm	Mineral oil and ester fluid (natural & synthetic)		Measurement Download	USB 2.0 Memory Stick
Ethane (C ₂ H ₆)	2 – 50,000 ppm	Robust design and portable			Direct Perception Sync
Ethylene (C ₂ H ₄)	2 – 50,000 ppm			Logfile Retrieval	USB 2.0 Memory Stick and Perception
Measurement Accuracy*	±5% or ±LDL (whichever is greater)	ENVIRONMENT		Output	CSV file format and Screen
Moisture (H ₂ O)	0-100% relative humidity	Operating Ambient Temperature	5 – 50 °C (+41 to +122 °F)	Hardcopy	2 inch thermal printer
Moisture in Oil Accuracy	±3%	Operating Altitude	Maximum 2,000m	Onboard Diagnostics	Duval's triangle, Rogers' ratio, Key Gas & Japanese ETRA
*Accuracy quoted is the accuracy of the detectors during calibration; gas-in-oil measurement accuracy may be affected by sampling, oil type, environmental conditions and/or product usage cycle.		Operating Pressure	760 – 1040 millibar	ADDITIONAL OPTIONS	
Note: For Buchholz gas samples, LDL is 50 ppm, accuracy is ±30%, for all gases.		Power Supply	115 – 230 V AC 50/60 Hz; 40 W	Gas check kit for verification of ongoing accuracy	
		Enclosure	IP67 (when closed) IP20 (when operating)	Kit for collection and analysis of Buchholz gas samples	
		Oil Sample Volume	50 ml (Oil)	Transit case provides extra protection during air travel and harsh environment transportation (IP67 rating when closed)	
		Gas Sample Volume	5 ml (Buchholz Gas)	Sample cooler box to rapidly cool hot oil samples for immediate analysis, doubles as a secure sample transportation container	
		Dimensions	363 mm x 282 mm x 120 mm (14.3 in. x 11.1 in. x 4.7 in.)		
		Weight	9 kg (20 lb)		

Kelman TRANSPORT X ²	TX2	x	x	x	x	x	x	Base Unit	Description
Language	ENG								English
Power Cable		CA1							IEC Mains cable - 2 Pin EURO
		CA2							IEC Mains cable - 3 Pin USA
		CA3							IEC Mains cable - Australian
		CA4							IEC Mains cable - South Africa + India
		CA5							IEC Mains cable - UK
		CA6							IEC Mains cable - Swiss
		CA7							IEC Mains cable - Japanese
Color option		CL0						Transport X2 CONF Silver	Standard - Silver
		CL1						Transport X2 CONF Yellow	Unit and accessories pack in yellow
Transit Case				TC0					None
				TC1				CASE01017	Unit and accessories packed in graphite transit case
System Check Kit					SC0				Not Required
					SC1			KITT00002	System Check Kit (including 1x gas canister)
Buchholz Kit						B0			Not Required
						B1		KITT00005	Buchholz Kit for Buchholz Gas Measurements

GE Grid Solutions
Lissue Industrial Estate East
Unit 1, 7 Lissue Walk
Lisburn BT28 2LU
United Kingdom
Tel: +44 (0) 2892 622915

GEGridSolutions.com

GE, the GE monogram, Kelman, Hydran and Perception are trademarks of the General Electric Company.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

© Copyright 2018, General Electric Company. All Rights Reserved.

Transport X2-DGA-Brochure-EN-2018-04-Grid-GA-1648



imagination at work